

Regd. Office :

A- 6, NAND Complex,
Near AIMS Oxygen, Juna Padra Road,
Baroda 390 020 - INDIA


Marketing / Customer Support :

5-6, 3rd Floor, Mrudula Sadan,
Pratap Road, Raopura,
Baroda 390 001 - INDIA

JUTRON Vision

enhancing vision ~ enriching life

Precision Vision[®] USA



5016 Pelli-Robson Trans-Illuminated Contrast Sensitivity Chart – Low Vision

The trans-illuminated versions are identical to the original “Gold Standard” Pelli-Robson Contrast Sensitivity Charts. These charts cover $\frac{3}{4}$ of the original contrast range and are manufactured to the same true log steps and use the same letters and letter sizes as the originals.

Trans-illumination has the advantage of uniform fixed illumination and eliminates the need for staging the room and verifying chart luminance with room lighting. These charts require using our ETDRS Illuminator Cabinet™, Cat. No. 2425 and our 85 cd/m² lamp filter, Cat No 2427D85.

Chart 5016 designated for Low Vision uses the upper 12 contrast levels ranging from 0 – 1.65 Log CS (100% – 2.2% Weber).